

**HDC-CM-2BPN2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Flexible and all-purpose – the proper solution for many applications**

ConCept is a modular system consisting of modules and frames. Together, they form a complete insert that can easily be integrated into an HDC housing.

The patented modular system allows you to put together individual connector variants.

A variety of modules for power, signal and data transmission are supplemented further by modules intended for pneumatics, and SC/LC cables.

The sturdy, one-piece module-frame design (optionally available in polycarbonate or die-cast zinc) and the integrated module-release aid both improve handling of the product.

**General ordering data**

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	<a href="#">1894750000</a>
Type	HDC-CM-2BPN2.5
GTIN (EAN)	4032248509225
Qty.	1 pc(s).

**HDC-CM-2BPN2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Height	40.4 mm	Height (inches)	1.591 inch
Width	11.4 mm	Width (inches)	0.449 inch
Length	34 mm	Length (inches)	1.339 inch
Net weight	26 g		

**Temperatures**

Limit temperature	-40 °C ... 80 °C
-------------------	------------------

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**ConCept Pneumatic module**

Colour	black	Connection cross-section (internal)	2.5 mm
Contact travel	4 mm	Hose type	Only use PTFE hoses
Module body material	PA 6.6	Number of valves	2
Sealing material	NBR	Shutoff	Yes
Test pressure	10 bar	UL 94 flammability rating	V-0

**Dimensions**

Height of socket	40.4 mm	Total length base	34 mm
Width	11.4 mm		

**General data**

Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Material	Polyamide, glass fibre-reinforced
Number of poles	2	Series	ConCept module
Type	Female	UL 94 flammability rating	V-0

**Version**

Material	Polyamide, glass fibre-reinforced	Type of connection	Hose connection (pneumatic)
----------	-----------------------------------	--------------------	-----------------------------

**Classifications**

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-01-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92

**Approvals**

Approvals



ROHS	Conform
------	---------

Creation date September 16, 2022 9:23:18 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

**HDC-CM-2BPN2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1894750000](#)