

SCREWTY M8 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Screwty® attachment is suitable for M8 round plug-in connectors, with an outside dimension of the knurled nut of 10 ± 0.3 mm. The tightening torque is 0.5-0.6 Nm.

General ordering data

Version	Cable gland tool for moulded M12 lines
Order No.	1900110000
Type	SCREWTY M8 KO O. SD
GTIN (EAN)	4032248409969
Qty.	1 pc(s).

Creation date January 29, 2022 2:23:24 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

SCREWTY M8 KO O. SD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 13 g

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-01-90-90		

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1900110000](#)