

IE-PS-V04P-RJ45-TH-BP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

PushPull plug-in connector set according to IEC
61076-3-106 ver.4 (IEC24702), plastic with RJ45 insert

General ordering data

Version	RJ45 crimp plug, Version 4, anti-kink device, Cat.6 _A / Class E _A (ISO/IEC 11801 2010)
Order No.	1963190000
Type	IE-PS-V04P-RJ45-TH-BP
GTIN (EAN)	4032248651672
Qty.	10 pc(s).

IE-PS-V04P-RJ45-TH-BP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	35 g
------------	------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1	SCIP	11b17e97-f803-4c09-9278-b20f22f15f81
------------	--	------	--------------------------------------

General data

Connection 1	RJ45	Connection 2	Crimp
Description of article	Version 4, anti-kink device	Housing main material	PA UL 94 V0
Insulation cross-section, min.	0.85 mm	Insulation cross-section, max.	1.05 mm
Category	Cat.6A / Class E _A (ISO/IEC 11801 2010)	Connection diameter, solid	0.36...0.51
Conductor connection cross-section, solid (AWG)	AWG 26/1...AWG 24/1	Connection diameter, flexible	0.46...0.61 mm
Conductor connection cross-section, flexible (AWG)	AWG 27/7...AWG 24/7	MICE classification M	M ₃
MICE classification I	I ₃	MICE classification C	C ₁
MICE classification E	E ₃	Sheath diameter, min.	5 mm
Sheath diameter, max.	10 mm	Shielding	360°; all-round enclosure
Protection degree	IP67		

General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-3-106 Var. 4, IEC 60603-7-51
-------------------------	---------	--------------------	--

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

IE-PS-V04P-RJ45-TH-BP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	GOST Approval ISO/IEC EN and TIA/EIA Screened Class EA Category 6A, 4 connector channel DUXR.E316369
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Product Change Notification	20210412 Technical change for cap nut V1 and V4 20210412 Technische Änderung zu Hutmutter V1 und V4
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Manual
Catalogues	Catalogues in PDF-format
Brochures	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN


IE-PS-V04P-RJ45-TH-BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Installation cut-out



Mounting cut-out: 1. With central screw connection / 2. For mounting with four M3 screws

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1963190000](#)