

**IE-PS-V04P-2LC-MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



PushPull plug-in connector set according to IEC  
61076-3-106 ver.4 (IEC24702), plastic with LC insert

**General ordering data**

Version	FO connector, Variant 4, LC-Duplex multi-mode, IP67
Order No.	<a href="#">1963320000</a>
Type	IE-PS-V04P-2LC-MM
GTIN (EAN)	4032248651795
Qty.	10 pc(s).

Creation date September 17, 2022 8:14:32 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

**IE-PS-V04P-2LC-MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	77.8 mm	Depth (inches)	3.063 inch
Height	20.1 mm	Height (inches)	0.791 inch
Width	20.2 mm	Width (inches)	0.795 inch
Net weight	3.1 g		

**Temperatures**

Operating temperature	-40 °C...70 °C
-----------------------	----------------

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1	SCIP	e5bbf197-73b5-420b-90c0-0173b7b
------------	---	------	---------------------------------

**General data**

Colour	Miscellaneous	Connection 1	LC
Connection 2	gluing, crimping, polishing	Description of article	Variant 4, LC-Duplex multimode
Fibre type	Multimode	Housing main material	PA UL 94 V0
Housing material, insert	PBT, Zinc diecast	Insertion loss	0.5 dB singlemode, 0.4 dB multimode
Plugging cycles	500	Protection degree	IP67
Return loss (attenuation)	40 dB singlemode; 30 dB multimode	Sheath diameter, max.	10 mm
Sheath diameter, min.	5 mm		

**General standards**

Connector standard	IEC 61076-3-106 Var. 4, IEC 61754-20
--------------------	--------------------------------------

**Classifications**

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

**Approvals**

Approvals



ROHS

Conform

**IE-PS-V04P-2LC-MM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

Approval/Certificate/Document of Conformity	<a href="#">GOST Approval</a>
Engineering Data	<a href="#">WSCAD</a>
Product Change Notification	<a href="#">20210412 Technical change for cap nut V1 and V4</a> <a href="#">20210412 Technische Änderung zu Hutmutter V1 und V4</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>


**IE-PS-V04P-2LC-MM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Dimensioned drawing**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1963320000](#)