

PAC-UNIV-HE20-F-8M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYY, 0.25 mm ²
Order No.	7789 100080
Type	PAC-UNIV-HE20-F-8M
GTIN (EAN)	8430243959612
Qty.	1 pc(s).

Creation date January 30, 2022 4:23:01 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

PAC-UNIV-HE20-F-8M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 834 g

Temperatures

Storage temperature -10...60 °C Operating temperature -10...50 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General Data

Cable	Cable LiYY	Cable length	8 m
Connector PLC side	H0.25/10 (FERRULES 0.25mm ²)	Interface connector	FLAT CABLE CONECTOR HE10 20P
Material	PVC	Number of poles, min.	20-pole
Outer diameter	8.6 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.25 mm ²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
High voltage test	1 KV/1s	Operating voltage	≤ 60 V DC ≤ 25 V AC
Permissible current strength per path, max.	1 A	Rated voltage	≤ 60 Vdc ≤ 25 Vac
Resistance	≤ 80 mΩ/m	Total current, max.	3 A

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20		

Approvals

Approvals



ROHS

Conform

Downloads

User Documentation	Colours chart
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789100080](#)