

**PAC-UNIV-HE20-LCH-1M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

Version	Pre-assembled cable, PAC, Cable LiYY, 0.14 mm <sup>2</sup>
Order No.	<a href="#">7789306010</a>
Type	PAC-UNIV-HE20-LCH-1M
GTIN (EAN)	8430243969062
Qty.	1 pc(s).

Creation date January 30, 2022 5:54:58 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

**PAC-UNIV-HE20-LCH-1M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 66 g

**Temperatures**

Storage temperature -10...60 °C Operating temperature -10...50 °C

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**General Data**

Cable	Cable LiYY	Cable length	1 m
Connector PLC side	FLAT CABLE CONECTOR HE10 20P	Interface connector	FLAT CABLE CONECTOR HE10 20P
Material	PVC	Number of poles, min.	20-pole
Outer diameter	8.6 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.14 mm <sup>2</sup>		

**Electrical Data**

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
High voltage test	1 KV/1s	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 150 mΩ/m
Total current, max.	3 A		

**Classifications**

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20		

**Approvals**

Approvals



ROHS Conform

**Downloads**Catalogues [Catalogues in PDF-format](#)

Brochures

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789306010](#)