

PAC-UNIV-HE20-LCF-2M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

| | |
|------------|--|
| Version | Pre-assembled cable, PAC, Cable LiYY, 0.14 mm ² |
| Order No. | 7789388020 |
| Type | PAC-UNIV-HE20-LCF-2M |
| GTIN (EAN) | 4032248992997 |
| Qty. | 1 pc(s). |

Creation date January 30, 2022 6:07:32 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

PAC-UNIV-HE20-LCF-2M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 143.6 g

Temperatures

Storage temperature -10...60 °C Operating temperature -10...50 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General Data

| | | | |
|--------------------|--|-----------------------|------------------------------|
| Cable | Cable LiYY | Cable length | 2 m |
| Connector PLC side | H0.25/10 (FERRULES 0.25mm ²) | Interface connector | FLAT CABLE CONECTOR HE10 20P |
| Material | PVC | Number of poles, min. | 20-pole |
| Outer diameter | 8.6 ± 1 mm | Suitable for | Digital signals |
| Wire cross-section | 0.14 mm ² | | |

Electrical Data

| | | | |
|------------------------|-------------------|---|------------|
| Capacity wire / shield | 300 pF/m | Capacity wire / wires | 300 pF/m |
| High voltage test | 1 KV/1s | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 Vdc ≤ 25 Vac | Resistance | ≤ 150 mΩ/m |
| Total current, max. | 3 A | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000237 | ETIM 7.0 | EC000237 |
| ETIM 8.0 | EC000237 | ECLASS 9.0 | 27-24-22-20 |
| ECLASS 9.1 | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | | |

Approvals

ROHS Conform

Downloads

User Documentation [Colours chart](#)
 Catalogues [Catalogues in PDF-format](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789388020](#)