



General ordering data

Order No.	9457660500
Part designation	SAIL-M12BG-2/4-5.0U
Version	Sensor/Actuator line, One end without connector, LED: No, 5.00 m, PUR/PVC
EAN	4008190311773
Qty.	1 pc(s).

Technical data

Ambient temperature, max.	80 °C
Ambient temperature, min.	-30 °C
Cable diameter, max.	5 mm
Cable diameter, min	4.6 mm
Connection cross-section	0.34
Contact material	Ni/Au
Contact surface	gold-plated
Contact tube diameter	M12
Core cross-section	0.34 mm ²
Material	PUR/PVC
Protection class	IP 67
Rated current	4 A
Rated voltage	250 V DC / 300 V AC
Sheathing colour	black
No. of poles	3
Version	Female socket, straight
Cable length	5 m

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000304
ETIM 3.0	EC001855
eClass 4.1	27-06-00-00
eClass 5.0	27-06-91-90
eClass 5.1	27-06-91-90

Similar products

Order No.	Part designation	Version
9457660300	SAIL-M12BG-2/4-3.0U	Sensor/Actuator line, One end without connector, LED: No, 3.00 m, PUR/PVC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9457660500](#)