



General ordering data

Order No.	9457790030
Part designation	SAIL-M12GM12W-3L0.3U
Version	Sensor/Actuator line, Connecting line, LED: Yes, 0.30 m, PUR/PVC
EAN	4032248227921
Qty.	1 pc(s).

Technical data

Ambient temperature, max.	80 °C
Ambient temperature, min.	-50 °C
Cable diameter, max.	5 mm
Cable diameter, min.	4.6 mm
Connection cross-section	0.34
Contact material	Ni/Au
Contact surface	gold-plated
Contact tube diameter	M12
Core cross-section	0.34 mm ²
Material	PUR/PVC
Protection class	IP 67
Rated current	4 A
Rated voltage	250 V DC / 300 V AC
Sheathing colour	black
Wiring diagram jumped	No
No. of poles	3
Version	pin, straight - socket, 90°
Cable length	0.3 m

Classifications

ETIM 2.0	EC000304
ETIM 3.0	EC001855
eClass 4.1	27-06-00-00
eClass 5.0	27-06-91-90
eClass 5.1	27-06-91-90

Classifications

Similar products

Order No.	Part designation	Version
9457790060	SAIL-M12GM12W-3L0.6U	Sensor/Actuator line, Connecting line, LED: Yes, 0.60 m, PUR/PVC
9457790090	SAIL-M12GM12W-3L0.9U	Sensor/Actuator line, Connecting line, LED: Yes, 0.90 m, PUR/PVC
9457790120	SAIL-M12GM12W-3L1.2U	Sensor/Actuator line, Connecting line, LED: Yes, 1.20 m, PUR/PVC
9457790150	SAIL-M12GM12W-3L1.5U	Sensor/Actuator line, Connecting line, LED: Yes, 1.50 m, PUR/PVC
9457791000	SAIL-M12GM12W-3L10U	Sensor/Actuator line, Connecting line, LED: Yes, 10.00 m, PUR/PVC
9457790100	SAIL-M12GM12W-3L1.0U	Sensor/Actuator line, Connecting line, LED: Yes, 1.00 m, PUR/PVC
9457790200	SAIL-M12GM12W-3L2.0U	Sensor/Actuator line, Connecting line, LED: Yes, 2.00 m, PUR/PVC
9457790300	SAIL-M12GM12W-3L3.0U	Sensor/Actuator line, Connecting line, LED: Yes, 3.00 m, PUR/PVC
9457790500	SAIL-M12GM12W-3L5.0U	Sensor/Actuator line, Connecting line, LED: Yes, 5.00 m, PUR/PVC
9457790250	SAIL-M12GM12W-3L2.5U	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9457790030](#)