

**PAC
PAC-UNIV-D50F-D50F-1M**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

Cable pre-confeccionado sub-d según IEC-807/
DIN41652

- Sub-d a Sub-d
- Sub-d a punteras
- Cable apantallado

General ordering data

Available until	2014-05-20
Type	PAC-UNIV-D50F-D50F-1M
Order No.	1349940010
Version	Pre-assembled cable, PAC, Cable LiYCY, 14,2 ± 1 mm
GTIN (EAN)	4032248160570
Qty.	1 pc(s).

PAC PAC-UNIV-D50F-D50F-1M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 460 g

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General Data

Connector PLC side	SUB-D FEMALE 50P	Interface connector	SUB-D FEMALE 50P
Number of poles, min.	50-pole	Outer diameter	14,2 ± 1 mm
Cable	Cable LiYCY	Cable length	1 m
Material	PVC	Wire cross-section	0.25 mm ²

Electrical Data

Rated voltage (text)	≤ 60 Vdc ≤ 25 Vac	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	≤ 80 mΩ/m

Classifications

ETIM 5.0	EC000237	ETIM 6.0	EC000237
eClass 6.2	27-24-92-05	eClass 7.1	27-24-92-05
eClass 8.1	27-24-92-05	eClass 9.0	27-24-22-20
eClass 9.1	27-24-22-20		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [CAT 4.5 ELECTR 16/17 EN](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1349940010](#)