

PAC
PAC-M340-SD15-V2-1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

General ordering data

| | |
|-----------------|---|
| Delivery status | Discontinued |
| Available until | 2014-05-20 |
| Type | PAC-M340-SD15-V2-1M |
| Order No. | 7789640010 |
| Version | Pre-assembled cable, PAC, Cable LiYCY, 0.25 mm ² |
| GTIN (EAN) | 4032248915811 |
| Qty. | 1 pc(s). |

Data sheet

PAC PAC-M340-SD15-V2-1M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 278.65 g

Temperatures

| | | | |
|-----------------------------|-------------|-----------------------------|-------------|
| Operating temperature, max. | 50 °C | Operating temperature, min. | -10 °C |
| Storage temperature, max. | 60 °C | Storage temperature, min. | -10 °C |
| Operating temperature | -10...50 °C | Storage temperature | -10...60 °C |

General Data

| | | | |
|-----------------------|-------------------------------|---------------------|----------------------|
| Connector PLC side | SCHNEIDER BMX FTB 2000 20P | Interface connector | SUB-D FEMALE 15P |
| Number of poles, min. | 15-pole | Outer diameter | 8.7 ± 1 mm |
| Cable | Cable LiYCY | Cable length | 1 m |
| Material | PVC | Wire cross-section | 0.25 mm ² |

Electrical Data

| | | | |
|----------------------|-------------------|--|-----------|
| Rated voltage (text) | ≤ 60 Vdc ≤ 25 Vac | Permissible current strength per path, max. | 1 A |
| Total current, max. | 3 A | Resistance | ≤ 80 mΩ/m |
| High voltage test | 1 KV/1s | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000237 | ETIM 5.0 | EC000237 |
| ETIM 6.0 | EC000237 | eClass 6.2 | 27-06-03-90 |
| eClass 7.1 | 27-24-92-05 | eClass 8.1 | 27-24-92-05 |
| eClass 9.0 | 27-24-22-20 | eClass 9.1 | 27-24-22-20 |

Approvals

Approvals



ROHS Conform

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789640010](#)