



Datasheet for part number KPT2E22-55SW-EW

Our Catalog Part Number: KPT2E22-55SW-EW	
Brand: Cannon	Product Category: Circular Product Line: 26482 - Style Series I & Mil Battery Series: KPT / SE

Product Datasheet	
Shell Style	Box mounting receptacle
Gender	Socket
Shell Size	22
Contact Arrangement	22-55
Number of contacts	55 contacts size 20
Contact Type	Solder Pin 0.6 x 7 mm
Contact Plating	Size 12 & 16: gold plated Size 20: Contact body: tin / Contact area: gold plated
Insulator Rotation	30°
Shell Material	Aluminium alloy
Shell Plating	Olive drab chromate over cadmium plating
Insulator and Gromet Material	Polychloroprene
Contact Material	Copper alloy
Water Tightness	Acc. To VG95319 Part 2, Test No. 5.9.2
Operating Temperature	-55°/+125°C (-67/257°F)
Mating Cycles	500 min
Vibration	200 m/s ² at 10 to 2000 Hz
Contact Rating AWG20	7,5 A
Insulator Resistance	≈5000 MOhm
Test Voltage	1500 Vrms
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.
Safety Provisions	IP67 acc. to DIN 40 050 (0,2 bar pressure over 48 hrs)
Salt Spray Resistance	500 hours salt spray resistant
General Info	<i>All tests in accordance with VG95319 and/or if applicable with VG95210</i>
Harnessing Info: Contact Cross-Section	See assembly instruction
Harnessing Info: Insulator Diameter	See assembly instruction

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ITT Cannon:](#)

[KPT2E22-55SWEW](#)