

Filament lamp

10-1412.1279



<https://eao.com/p/10-1412.1279>

Your product:



10-1412.1279 Filament lamp

OPERATING-/INDICATION PART

Illumination colour: White

ELECTRICAL CHARACTERISTICS

Operating voltage: 24 V AC/DC

Operation current: 50 mA \pm 10 %

Lumi. Intensity: mcd

MECHANICAL CHARACTERISTIC

Weight: 0.002 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER

Short Description: Filament lamp, BA9s, White, 24 V AC/DC

Hints: The max. overall length of the lamp may not exceed 28 mm











Wiring diagrams:

x_2^+



x_1^-

Where to Buy

	Distributor	Quantity in Stock	
	Newark	1172 in stock	Buy 
	element14 Singapore	1172 in stock	Buy 
	Farnell UK	1172 in stock	Buy 
	DigiKey	998 in stock	Buy 
	Mouser Electronics	704 in stock	Buy 

[Show more](#) 

Powered by oemsecrets.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[10-1412.1279](#)