


**BB-9PAMF1**  
**BB-9PAMF3**  
**BB-9PAMF6**

**BB-9PAMF10**  
**BB-9PAMF15**  
**BB-9PAMF25**

## DB9M to DB9F Serial Cables



### Features

- Fully molded backshell with strain relief for extra protection
- 28 AWG stranded conductors for flexibility
- Thumbscrews for tool-less termination
- DB9 male to DB9 female
- REACH, RoHS-3 (2011/65/EU amended by 2015/863/EU)


### Introduction

These ready-to-use serial cables feature fully molded backshells, strain relief protection, and thumbscrews. Suitable for connecting 9-pin serial devices to laptops, computers and more. Choose from 0.3 to 7.6 meter lengths (1 to 25 ft).

### Ordering Information

Model No.	Description	Length
<b>BB-9PAMF1</b>	Serial Cable, DB9 Male to DB9 Female	0.3m (1 ft)
<b>BB-9PAMF3</b>	Serial Cable, DB9 Male to DB9 Female	0.9m (3 ft)
<b>BB-9PAMF6</b>	Serial Cable, DB9 Male to DB9 Female	1.8m (6 ft)
<b>BB-9PAMF10</b>	Serial Cable, DB9 Male to DB9 Female	3.1m (10 ft)
<b>BB-9PAMF15</b>	Serial Cable, DB9 Male to DB9 Female	4.6m (15 ft)
<b>BB-9PAMF25</b>	Serial Cable, DB9 Male to DB9 Female	7.6m (25 ft)

### Dimensions



P1	1006	P2
1	—	1
2	—	2
3	—	3
4	—	4
5	—	5
6	—	6
7	—	7
8	—	8
9	—	9
SHIELD	—	SHIELD

\*NOTE: All relevant materials are complied with RoHS directive .

5	BLACK PVC TUBE #3.0*22mm
	ALUMINUM FOIL 33*65mm
	MOLDED PE COLOR TRANSPARENT
	MOLDED PVC BEIGE
4	NON-UL 9C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BEIGE, DRAWING NO. EMAL2809C-051
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE
2	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR
1	DB9 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-9PAMF25](#)