

Datasheet

CELLULAR (2G/3G/4G) Antenna

BB-CEL8026STAT

- Outdoor antenna for fix wall mounting
- Omnidirectional radiation



Subject to alterations

Technical data




Dimensions	275 mm x 16 mm (without bracket)	
Weight	355 g	
Housing Material	PE UV-resistant	
Bracket Material	stainless steel	
Temperature range	-30° C - + 80° C	
Protection class	IP66 (acc. IEC 60529)	
CELLULAR		
Frequency range	LTE (low): CELL (low): CELL (high): LTE (high):	790 to 862 MHz 824 to 960 MHz 1710 to 2170 MHz 2500 to 2690 MHz
Impedance	50 Ohm	
Gain	5.1 dBi	
Return loss (VSWR)	< 2,0	
Radiation pattern	omnidirectional (horizontal)	
Load capacity	max.	10 W (c.w.)
Polarization	vertical	
Cable type	RG 58	
Cable length	5000 +50 mm	
Connector	SMA male	

Datasheet

CELLULAR (2G/3G/4G) Antenna

BB-CEL8026STAT

Technical drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-CEL8026STAT](#)