

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA 66
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
METAL HOUSING: BRASS (CuZn)
TERMINAL SCREW: STEEL ZINC PLATING
TERMINAL SCREW SLOT TYPE: "-"
WIRE GUARD: PhBz TIN PLATED

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL	cULus	VDE
CURRENT RATING:	10A	10.5A
WORKING VOLTAGE:	300VAC	300VAC
WITHSTANDING VOLTAGE:	1.6KV	2.5KV
CONTACT RESISTANCE:	□ 20 mOhm max	

MECHANICAL
SOLID WIRE: 26-16 AWG / 0.13-1.5MM²
STRANDED WIRE: 26-16 AWG / 0.13-1.5MM²
TORQUE: 3.0Lb-In / 0.34Nm



WIRE STRIPE LENGTH: 6-7MM
SCREW: M2.0
PITCH: 3.5MM

PACKAGING: BOX

SERIE 3611

CERTIFICATION



RoHS Compliant				<div>PROJECTION:</div> <div></div>	<div>GENERAL TOLERANCE</div> <div>.X = \pm 0.2</div> <div>.XX = \pm 0.15</div>	<div></div>		D	
G									
F									
E									
D				APPROVAL: RJ	UNIT: MM	DESCRIPTION: SERIE 3611 - 3.50MM VERTICAL CABLE ENTRY PLUG 1.5MM² WIRES WR-TBL	SIZE A4		
C					SCALE:				
B					SHEET: 1/1				WERI PART NO: 691 361 100 0xx
A	31-OCT-08	PDF	JP		DRAW: MARVIN				
REV	DATE	FILE	BY						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-CON-CR3P-TB](#)