

EKI-9728G-4X8CI

Industrial Rackmount L3 Managed Switch with AC/DC



Features

- 16 x Gigabit RJ-45 ports + 4 x 10GbE SFP ports + 8 x Gigabit combo ports
- L3 function: Static route, RIP, OSPF, VRRP, PIM-SM, PIM-DM
- SFP socket for easy and flexible fiber expansion
- Management: SNMP v1/v2c/v3, WEB, Telnet, standard MIB
- Security: 802.1x HTTPS, SSH, and SNMPv3
- Dual power input and 2 x relay output
- Wide operating temperature range of -40 ~ 85°C
- Redundancy protocols: Gigabit X-Ring Pro (ultra high-speed recovery time < 20 ms), RSTP/STP (802.1w/1D), MSTP

Introduction

The EKI-9728G is an L3 management switch that supports RIP v1/v2, OSPF v1/v2/v3, and VRRP. Its wide operating temperature of -40 ~ 85°C means that it can operate reliably in harsh environments. Designed with 16 Gigabit ports, 4 10GbE SFP ports, and 8 Gigabit combo ports, this unit provides abundant and flexible connection options. Finally, the EKI-9728G series feature dual power inputs to ensure system stability, and 2 relay outputs for greater user flexibility.

Specifications

Communications

- **Standard** IEEE 802.3, 802.3u, 802.3x, 802.3z, 802.1D, 802.1w, 802.1p, 802.1Q, 802.1X, 802.3ad, 802.3ab
- **10G SFP+ (P1-4)** Supports 1GBASE or 10GBASE SFP (*compatible with SERDES SFP interface)
- **Combo ports (P21-28)** 10/100/1000BASE-TX, optional 100BASE or 1GBASE SFP (*compatible with SGMII or SERDES SFP interface)
- **Transmission Distance** Ethernet: Up to 100 m (4-wire Cat.5e, Cat.6 RJ45 cable suggested for Gigabit port)
SFP: Up to 110 km (depends on SFP)

Interface

- **Connectors** 16 x RJ45 (Ethernet)
8 x RJ45/SFP combo ports
4 x SFP+ ports
3-pin removable screw terminal (Power)
4-pin removable screw terminal (Relay)
- **LED Indicators** 10/100T (X): Link/Activity, Duplex/Collision
Gigabit Copper: Link/Activity, Speed (1000 Mbps)
SFP: Link/Activity
- **Console** RS-232 (RJ45)

Mechanism

- **Enclosure** IP30, metal shell with solid mounting kits
- **Dimensions (W x H x D)** 442 x 44 x 352 mm (17.4" x 1.73" x 13.85")
- **Mounting** 1U 19" Rack mount

Power

- **Power Consumption** 19.24 W @ 110V_{AC}
- **Power Input** 90 ~ 264AC/88 ~ 370V_{DC}
- **Fault Output** 2 Relay Outputs

Protection

- **Power Reverse** Present
- **Overload Current** Present

Environment


- **Operating Temperature** -40 ~ 85°C (-40 ~ 185°F)
- **Storage Temperature** -40 ~ 85°C (-40 ~ 185°F)
- **Operating Humidity** 5~95% (non-condensing)
- **Storage Humidity** 5~95% (non-condensing)

Certification

- **EMI** CE FCC EN55011, EN55032
- **Safety** EN62368-1
- **EMS** EN 61000-4-2
EN 61000-4-3
EN 61000-4-4
EN 61000-4-5
EN 61000-4-6
EN 61000-4-8
- **Shock** IEC 60068-2-27
- **Freefall** IEC 60068-2-32
- **Vibration** IEC 60068-2-6

Dimensions

Unit: mm



L2 Features

- **L2 MAC Address** 16K
- **Jumbo Frame** 12KB
- **VLAN Group** 4093 (VLAN ID 1-4093)
- **VLAN** Mac based VLAN, Protocol based VLAN, IP subnet based VLAN, Port based VLAN, GVRP
- **Port Mirroring** Per port, Multi-source port
- **IP Multicast** IGMP Snooping v1/v2/v3, MLD Snooping, IGMP Immediate leave
- **Storm Control** Broadcast, Multicast, Unknown unicast
- **Spanning Tree** IEEE 802.1D-STP, IEEE 802.1s-MSTP, IEEE 802.1w-RSTP, X-Ring Pro

QoS

- **Priority Queue Scheduling** WRR (Weighted Round Robin), SP (Strict Priority)
- **Class of Service** IEEE 802.1p based CoS, IP TOS, DSCP based CoS
- **Rate Limiting** Egress Rate limit, Ingress Rate limit
- **Link Aggregation** IEEE 802.3ad Dynamic Port Trunking, Static Port Trunking

Security

- **Port Security** Static, Dynamic
- **Authentication** 802.1x (Port-Based), RADIUS, TACACS+
- **Advanced Security** IP Source Guard

Management

- **DHCP** Client, Server
- **Access** SNMP v1/v2c/v3, WEB, Telnet, RMON, Standard MIB, Private MIB
- **Security Access** SSH 2.0, SSL
- **Software Upgrade** TFTP, HTTP, Dual Image
- **NTP** SNTP client
- **Unicast Routing** Static Route, RIP, OSPF
- **Multicast Routing** PIM-SM, PIM-DM
- **Routing Redundancy** VRRP

Ordering Information

- **EKI-9728G-4X8CI-AE** Ind. Rackmount L3 Managed Switch with AC/DC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[EKI-9728G-4X8CI-AE](#)