


SMD POWER INDUCTORS





• Features

1. Open frame construction.

ELECTRICAL CHARACTERISTICS



Part Number	Inductance (uH) (1)	Test Frequency	DC Resistance (Ω MAX) (2)	Saturation Current (A) (3)	Temperature Current (A) (4)
SC73-100	10	2.52MHZ	80m	1.44	2.40
SC73-120	12	2.52MHZ	90m	1.39	2.20
SC73-150	15	2.52MHZ	100m	1.24	2.00
SC73-180	18	2.52MHZ	110m	1.12	1.80
SC73-220	22	2.52MHZ	130m	1.07	1.65
SC73-270	27	2.52MHZ	150m	0.94	1.50
SC73-330	33	2.52MHZ	170m	0.85	1.40
SC73-390	39	2.52MHZ	220m	0.74	1.30
SC73-470	47	2.52MHZ	250m	0.68	1.22
SC73-560	56	2.52MHZ	280m	0.64	1.13
SC73-680	68	2.52MHZ	330m	0.59	1.05
SC73-820	82	2.52MHZ	410m	0.54	0.96
SC73-101	100	1KHZ	480m	0.51	0.88
SC73-121	120	1KHZ	540m	0.49	0.80
SC73-151	150	1KHZ	750m	0.40	0.72
SC73-181	180	1KHZ	1.02	0.36	0.62
SC73-221	220	1KHZ	1.20	0.31	0.54
SC73-271	270	1KHZ	1.31	0.29	0.48
SC73-331	330	1KHZ	1.50	0.28	0.44



(1). Inductance tolerance $\pm 20\%$ tested at 0.25V, 0ADC and 25°C.

(2). DCR measured at 25°C.

(3). The DC current at which the inductance decreases by 10% from its initial value.

(4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bel:](#)

[SC73-271](#) [SC73-820](#) [SC73-181](#) [SC73-470](#) [SC73-560](#) [SC73-150](#) [SC73-180](#) [SC73-151](#) [SC73-121](#) [SC73-221](#)
[SC73-390](#) [SC73-101](#) [SC73-330](#) [SC73-120](#) [SC73-220](#) [SC73-100](#) [SC73-331](#) [SC73-270](#) [SC73-680](#)