




MILITARY PART NO.	NSN	"A°"	"B°"	"C°"
M49142/04-0004	5935013185146	120	120	120
M49142/04-0104	5935014828780	110	140	110
M49142/04-0204	-	135	135	90

REV	ECO	DATE
J	54813	12/12/2013
K	57958	7/13/2021
L	58909	1/18/2024



M49142/04-0104 SHOWN


NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:

- 1.1 BODY: SILVER PLATED BRASS
- 1.2 DIELECTRICS: PTFE (TEFLON)
- 1.3 INNER SHIELD: GOLD PLATED BRASS
- 1.4 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
- 1.5 GASKET: SILICONE RUBBER
- 1.6 MOUNTING HARDWARE: SILVER PLATED COPPER ALLOY

2. ELECTRICAL:

- 2.1 FREQUENCY (MAX): 500 MHZ
- 2.2 IMPEDANCE: NON-CONSTANT



<p>NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.</p> <p>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018</p>	Model No:	M49142/04-0X0X	Title: TROMPETER	
	RoHS2	2011/65/EU	Drawing No. 3-0328	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH	3RD ANGLE PROJECTION	REV. L	
	ENGINEER: C. MONAHAN	Date: 1/18/2024	Size: A	DO NOT SCALE DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[M49142/04-0104](#)