

Essential Modular Jacks

Stewart Connector's Essential Line of modular jacks are ideal solutions for common modular jack applications. Stewart Connector's Essential modular jacks support the transmission of Gigabit Ethernet signals targeted to hubs, switches and routers. This line of modular jacks includes both right angle and vertical thru-hole mount options for 4, 6, and 8 position in shielded and unshielded modular jacks.

Features & Benefits

- 15 micro-inches of gold plating in contact mating area
- Voltage rating 125 VAC RMS
- Current rating 1.5 AMP
- Storage and operational temperature -40°- 80°

Applications

- Routers
- Servers
- Consumer products
- Telecom applications
- Standard office equipment



Essential Modular Jacks

Part Number	Orientation	Flange	Ports	Shield	Positions	Contacts
SS-90000-001	Horizontal	None	1	Unshielded	8	8
SS-90000-002	Horizontal	Flange	1	Unshielded	8	8
SS-90000-003	Horizontal	None	1	Unshielded	6	6
SS-90000-004	Horizontal	Flange	1	Unshielded	6	6
SS-90000-005	Vertical	None	1	Unshielded	6	4
SS-90000-006	Horizontal	Flange	1	Unshielded	6	4
SS-90000-007	Vertical	Flange	1	Unshielded	6	6
SS-90000-009	Horizontal	None	1	NF	8	8
SS-90000-010	Vertical	None	1	N/A	6	6
SS-90000-011	Horizontal	None	1	NF	8	8
SS-90000-012	Horizontal	None	1	NF	8	8
SS-90000-013	Vertical	None	1	NF	8	8
SS-90000-014	Vertical	None	1	N/A	8	8



11118 Susquehanna Trail South
 Glen Rock, PA 17327-9199

+1 717.235.7512
 techhelp@belf.com
belfuse.com/stewart-connector

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bel:](#)

[SS-90000-001](#) [SS-90000-002](#) [SS-90000-003](#) [SS-90000-004](#) [SS-90000-005](#) [SS-90000-006](#) [SS-90000-007](#) [SS-90000-009](#) [SS-90000-010](#) [SS-90000-011](#) [SS-90000-012](#) [SS-90000-014](#)