


Flange Mount Types - High Performance

DC - 18 GHz Flange Mount 523 Series		Model Numbers
Male/Female	Female/Female	Male/Male
ATT-0523-XX-SMA-02	ATT-523F-XX-SMA-02	ATT-523M-XX-SMA-02
XX = Attenuation Value: Select 01-30dB in 1dB increments (.5 dB increments available)		
HIGH PERFORMANCE		



DC - 12.4 GHz Flange Mount 524 Series		Model Numbers
Male/Female	Female/Female	Male/Male
ATT-0524-XX-SMA-02	ATT-524F-XX-SMA-02	ATT-524M-XX-SMA-02
XX = Attenuation Value: Select 01-30dB in 1dB increments (.5 dB increments available)		
HIGH PERFORMANCE		

SPECIFICATIONS - HIGH PERFORMANCE

Attenuation Accuracy: 1-6 dB ± 0.3 dB
 7-20 dB ± 0.5 dB
 21-30 dB ± 1.0 dB


VSWR: 1.07+.015(f GHz) max

Power: 2 Watts Average @ +25 °C derated linearly
 to .5 watts @ +125 °C and 200 Watts peak


Operating Temperature Range: -65 to +125 °C

Finish: Passivated Stainless Steel


DC - 8.0 GHz Flange Mount 531 Series		Model Numbers
Male/Female	Female/Female	Male/Male
ATT-0531-XX-SMA-02	ATT-531F-XX-SMA-02	ATT-531M-XX-SMA-02
XX = Attenuation Value: Select 01-30dB in 1dB increments (.5 dB increments available)		
HIGH PERFORMANCE		



DC - 4.0 GHz Flange Mount 525 Series		Model Numbers
Male/Female	Female/Female	Male/Male
ATT-0525-XX-SMA-02	ATT-525F-XX-SMA-02	ATT-525M-XX-SMA-02
XX = Attenuation Value: Select 01-30dB in 1dB increments (.5 dB increments available)		
HIGH PERFORMANCE		



DC - 2.0 GHz Flange Mount 526 Series		Model Numbers
Male/Female	Female/Female	Male/Male
ATT-0526-XX-SMA-02	ATT-526F-XX-SMA-02	ATT-526M-XX-SMA-02
XX = Attenuation Value: Select 01-30dB in 1dB increments (.5 dB increments available)		
HIGH PERFORMANCE		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[ATT-0523-05-SMA-02](#)