

Specification Sheet

Part Number: MK9PUA

Tool made of heavy duty parts to ensure optimum performance in demanding environments.

Ideal for heavy-duty ties (T50-T250), clamp and button head ties.

Same ergonomic improvements as the MK7P.

Low weight, comfortable grip and easy trigger depression.

Very durable, with adjustable, easy to read tension settings.

Lock-out features available.

Comes with lower air attachment, and optional upper air attachment.



MK9 Pneumatic, Top Air Supply Connection, Plastic Housing, 1/Pkg

Article Number 110-09112

Type MK9P

Color Black (BK)

Quantity Per carton

Product Description	The Mark 9 Pneumatic (MK9P) is constructed with heavy duty parts to ensure that it performs optimally in demanding environments. It is ideally designed to apply heavy-duty ties (T50-T250), clamp and button head ties. Like the MK7P, HellermannTyton's MK9P incorporates the next level of ergonomic improvement with its low weight, comfortable grip and easy trigger depression. Very durable, the pneumatic MK9P features adjustable, easy to read tension settings. Lock-out features are available. The MK9P is available with lower air attachment (standard) or can be ordered with an upper air attachment.
Short Description	MK9 Pneumatic, Top Air Supply Connection, Plastic Housing, 1/Pkg
Global Part Name	MK9P-PA66GF30-BK
Cable Ties	T50 thru T250 Series CTT20 thru CTT175 Series EI-TY Series Button Head Series
Cycle Time	2 strokes per second
Tension Setting Tools	Adjustable
Cable Tie Width Max (Imperial)	0.5
Power Supply	Dry or lubricated air
Material	Polyamide 6.6, glass fiber reinforced (PA66GF30%)
Material Shortcut	PA66GF30
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use

Reach Compliant (Article 33) No

ROHS Compliant Yes

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 8467195090

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[MK9PUA](#)