

## Specification Sheet

Part Number: 111-01302

The 316 grade stainless steel offers excellent resistance to salt spray, corrosion, weather and chemicals.

Self-locking, ball bearing mechanism for quick and easy installation, either by hand or tensioning tool.

Fully enclosed head prevents debris from interfering with locking mechanism.

High tensile strength for maximum strength and safety in heavy duty applications.



Stainless Steel Tie, 20.5" Long, 922lb Tensile Strength, SS316, Metal, 50/pkg

Article Number 111-01302

Type MBT20UH

Color Metal (ML)

Quantity Per bag

**Product Description**

HellermannTyton's Stainless Steel Ties are designed with a ball bearing locking mechanism to ensure high tensile strength and easy insertion when securing hoses, cables, pipes and more. Stainless steel ties can be used in virtually any indoor, outdoor or underground application. Grade 316 material is highly resistant to corrosion and widely used in marine environments where chemicals, salts, acids and temperature extremes may affect the bundling application.

Short Description	Stainless Steel Tie, 20.5" Long, 922lb Tensile Strength, SS316, Metal, 50/pkg
Global Part Name	MBT20UH-SS316L-ML
Minimum Tensile Strength (Imperial)	922
Minimum Tensile Strength (Metric)	4100
Length L (Imperial)	20.5
Length L (Metric)	521.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	ball bearing lock
Variant	Not Serrated
Width W (Imperial)	0.63
Width W (Metric)	16.0
Bundle Diameter Min (Imperial)	0.47
Bundle Diameter Min (Metric)	12.0
Bundle Diameter Max (Imperial)	5.98
Bundle Diameter Max (Metric)	152.0

Thickness T (Imperial)	0.01
Thickness T (Metric)	0.3
Material	Stainless Steel (SS316L)
Material Shortcut	SS316L
Flammability	Non-burning
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	7326908695

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[111-01302](#)