

Specification Sheet

Part Number: T18L0VOC2



Feature a UL 94 V-0 rating to comply with low flame and smoke requirements.

Inside serrations provide strong grip on cables and wire bundles.

Easy application either manually or with a tensioning tool.

Bent tail ensures a quick and simple installation.

Flame Retardant Cable Tie, 8" Long, UL Rated, 18lb Tensile Strength, PA66V0, Black, 100/pkg

Article Number 111-02044

Type T18L

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's flame retardant cable ties meet the UL 94 V-0 flammability requirements. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Flame Retardant Cable Tie, 8" Long, UL Rated, 18lb Tensile Strength, PA66V0, Black, 100/pkg

Global Part Name T18L-PA66V0-BK

Minimum Tensile Strength (Imperial) 18

Minimum Tensile Strength (Metric) 80

Length L (Imperial) 8.0

Length L (Metric) 205.0

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.10

Width W (Metric) 2.5

Bundle Diameter Min (Imperial) 0.12

Bundle Diameter Min (Metric) 3.0

Bundle Diameter Max (Imperial) 2.17

Bundle Diameter Max (Metric) 55.0

Thickness T (Metric) 1.2

Cable Tie Head Length (Imperial)	0.19
Cable Tie Head Width (Imperial)	0.18
Height H (Imperial)	0.15
Height H (Metric)	3.9
Material	Polyamide 6.6 V0 (PA66V0)
Material Shortcut	PA66V0
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +212°F (-40°C to +100°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes

UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T18L0VOC2](#)