

## Specification Sheet

Part Number: CTT60R0HSM4



Head design contains clamping rails to provide full circumferential compression around bundles.

Bent tail allows for quick insertion into head.

Clamp Tie, 8" Long, 60lb Tensile Strength, PA66HS, Black, 1000/pkg

Article Number 112-52114

Type CTT60R

Color Black (BK)

Quantity Per bag

Product Description The 360 degree compression ties are designed with underside clamping rails to allow for optimal surface contact and complete circumferential compression around the bundle. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Clamp Tie, 8" Long, 60lb Tensile Strength, PA66HS, Black, 1000/pkg

Global Part Name CTT60R-PA66HS-BK

Minimum Tensile Strength (Imperial)	60
Minimum Tensile Strength (Metric)	267
Length L (Imperial)	8.0
Length L (Metric)	203.2
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Thickness T (Metric)	1.2

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global

customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin.  
([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTT60R0HSM4](#)