

## Specification Sheet

Part Number: T50MI0M4



Mount design secures firmly with any #10 screw

Screw mount style creates low insertion and high extraction force

1-Piece Cable Tie/Screw Mount, 12.4" Long, #10 Screw, 3.4" Max Bundle Dia, 50lb, PA66, Black, 1000/pkg

Article Number 113-00031

Type T50MI

Color Black (BK)

Quantity Per bag

Product Description One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.

Short Description 1-Piece Cable Tie/Screw Mount, 12.4" Long, #10 Screw, 3.4" Max Bundle Dia, 50lb, PA66, Black, 1000/pkg

Global Part Name T50MI-PA66-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	12.4
Length L (Metric)	315.0
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	3.45
Bundle Diameter Max (Metric)	85.0
Height H (Imperial)	.23

Height H (Metric)	5.70
Mounting Hole Diameter D (Imperial)	0.22
Mounting Hole Diameter D (Metric)	5.5 mm
Mounting Hole Diameter D Max (Metric)	5.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Plenum Rating	AH-2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes

UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T50MI0M4](#)