

## Specification Sheet

Part Number: SR255X0HIHSUVC2

High impact, heat and UV stabilized releasable cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration.

Special design offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.



Releasable Cable Tie, 14.6" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 100/pkg

Article Number 115-00157

Type SR255X

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton SR255 Series heavy-duty cable ties offer a release feature in the head allowing for easy installation with the use of a cable tie tool. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force.

Short Description Releasable Cable Tie, 14.6" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 100/pkg

Global Part Name SR255X-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 250

Minimum Tensile Strength (Metric) 1115

Length L (Imperial) 14.6

Length L (Metric) 370.0

Fixation Method Releasable Cable Tie

Identification Plate Position none

Releasable Closure Yes

Width W (Imperial) 0.5

Width W (Metric) 12.6

Bundle Diameter Min (Imperial) 0.51

Bundle Diameter Min (Metric) 13.0

Bundle Diameter Max (Imperial) 3.94

Bundle Diameter Max (Metric) 100.0

Cable Tie Width Max (Imperial) 0.49

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[SR255X0HIHSUVC2](#)