

Specification Sheet

Part Number: SR255X0HIHSUVX2

High impact, heat and UV stabilized releasable cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration.

Special design offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.



Releasable Cable Tie, 14.6" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Article Number 115-42101

Type SR255X

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton SR255 Series heavy-duty cable ties offer a release feature in the head allowing for easy installation with the use of a cable tie tool. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force.

Short Description Releasable Cable Tie, 14.6" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Global Part Name SR255X-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 250

Minimum Tensile Strength (Metric) 1115

Length L (Imperial) 14.6

Length L (Metric) 370.0

Fixation Method Releasable Cable Tie

Identification Plate Position none

Releasable Closure Yes

Width W (Imperial) 0.5

Width W (Metric) 12.6

Bundle Diameter Min (Imperial) 0.51

Bundle Diameter Min (Metric) 13.0

Bundle Diameter Max (Imperial) 3.94

Bundle Diameter Max (Metric) 100.0

Cable Tie Width Max (Imperial) 0.49

Cable Tie Width Max (Metric) 12.5

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[SR255X0HIHSUVX2](#)