

Specification Sheet

Part Number: RT250S9X2



Special extended-pawl design offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Buckle feature on head allows excess strap to be tucked away after installation.

Releasable Cable Tie, Release Tab, 9.1" Long, 250 lb Tensile Strength, PA66, Natural, 25/pkg

Article Number 131-75819

Type RT250S

Color Natural (NA)

Quantity Per bag

Product Description HellermannTyton heavy-duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Releasable Cable Tie, Release Tab, 9.1" Long, 250 lb Tensile Strength, PA66, Natural, 25/pkg

Global Part Name	RT250S-PA66-NA
Minimum Tensile Strength (Imperial)	250
Minimum Tensile Strength (Metric)	1115
Length L (Imperial)	9.1
Length L (Metric)	230.0
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.49
Width W (Metric)	12.5
Bundle Diameter Min (Imperial)	0.47
Bundle Diameter Min (Metric)	12.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0

Thickness T (Imperial)	0.075
Thickness T (Metric)	1.9
Cable Tie Head Length (Imperial)	0.88
Cable Tie Head Width (Imperial)	0.79
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25

Package Quantity (Metric) 25

Customs Number 3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[RT250S9X2](#)