

## Specification Sheet

Part Number: 133-00997



Separates and secures bundles avoiding abrasion.

Designed to handle both convoluted tubing and bundles not covered in convoluted tubing.

Available in a variety of sizes and colors to be easily identified.

HC Clamp Bundle Separator, Two Hole, PA66HIRGF13, Red, 500/pkg

Article Number 133-00997

Type HC2E

Color Red (RD)

Quantity Per bag

Product Description HC Clamps separate multiple bundles and secure them to brackets or frame rails. Each mount has two pawls for easy pre-installation on a threaded fastener prior to securing with a mechanical fastener. HC Clamps have ribs that make them ideal for convoluted tubing, but they can also be used to separate separate bundles that aren't protected with convoluted tubing.

Short Description HC Clamp Bundle Separator, Two Hole, PA66HIRGF13, Red, 500/pkg

Global Part Name HC2E-PA66HIRGF13-RD

|   |         |
|---|---------|
| Length L (Imperial)                     | 2.747   |
| Length L (Metric)                       | 67.77   |
| Width W (Imperial)                      | 1.1     |
| Width W (Metric)                        | 27.94   |
| Bundle Diameter Min (Imperial)          | 0.51    |
| Bundle Diameter Min (Metric)            | 13.03   |
| Bundle Diameter Max (Imperial)          | 0.51    |
| Bundle Diameter Max (Metric)            | 13.03   |
| Bundle Diameter 1st Loop Max (Imperial) | 0.513   |
| Bundle Diameter 1st Loop Max (Metric)   | 13.03   |
| Bundle Diameter 2nd Loop Max (Imperial) | 0.513   |
| Bundle Diameter 2nd Loop Max (Metric)   | 13.03   |
| Height H (Imperial)                     | 1.38    |
| Height H (Metric)                       | 34.94   |
| Mounting Hole Diameter D (Imperial)     | 0.32    |
| Mounting Hole Diameter D (Metric)       | 8.12 mm |

|                              |   |
|------------------------------|---|
| Material                     | Polyamide 6.6, high impact modified, glass-fiber reinforced (PA66HIRGF13) |
| Material Shortcut            | PA66HIRGF13   |
| UV Resistant (Yes/No)        | No  |
| Use Conditions               | For Indoor and Outdoor Use  |
| Operating Temperature        | -40°F to +257°F (-40°C to +125°C)   |
| Reach Compliant (Article 33) | No  |
| ROHS Compliant               | Yes   |
| Package Quantity (Imperial)  | 500   |
| Package Quantity (Metric)    | 500   |
| Customs Number               | 3926909988  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[133-00997](#)