

## Specification Sheet

Part Number: 151-00838



Designed for use with MBTS(-S), MBTH(-S), and MBTSFC stainless steel ties, or 18 through 120 pound nylon cable ties to provide stability when securing bundles.

Secures with a single screw providing quick installation.

Stainless Steel Tie Mount, .21" Hole Dia, .39" Max Tie Width, Grade 316 SST, ML, 100/pkg

**Article Number** 151-00838

**Type** SSPC5

**Color** Metal (ML)

**Quantity Per** bag

**Product Description** Stainless steel P-mounts provide a robust and extremely durable fixing solution for a wide range of applications. With a 10mm slot width and either a 4mm, 5mm or 6mm fixing hole, this '2-way' mount can be installed quickly and easily with a single screw or bolt providing excellent performance and a high pull force. Designed for heavy duty applications and made out of a high grade stainless steel 316 material, these P-mounts provide resistant to chemicals, salt spray, extreme weather conditions and corrosion. They are also non-flammable, ensuring a highly secure and safe fixing solution.

<b>Short Description</b>	Stainless Steel Tie Mount, .21" Hole Dia, .39" Max Tie Width, Grade 316 SST, ML, 100/pkg
<b>Global Part Name</b>	SSPC5-SS316-ML
<b>Length L (Imperial)</b>	0.91
<b>Length L (Metric)</b>	23.0
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	0.40
<b>Width W (Metric)</b>	10.2
<b>Cable Ties</b>	MBTS(-S) and MBTH(-S) stainless steel ties
<b>Height H (Imperial)</b>	0.18
<b>Height H (Metric)</b>	4.5
<b>Cable Tie Width Max (Imperial)</b>	0.39
<b>Cable Tie Width Max (Metric)</b>	10.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.21
<b>Mounting Hole Diameter D (Metric)</b>	5.3 mm
<b>Mounting Hole Diameter D Max (Metric)</b>	5.3

<b>Material</b>	Stainless Steel (SS316)
<b>Material Shortcut</b>	SS316
<b>Flammability</b>	Non-burning
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-112°F to +1000°F (-80°C to +538°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	7326908695

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00838](#)