

Specification Sheet

Part Number: 151-00950

KR/CTM series are designed to provide stability to wire bundles. These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.



Metal Cnt Cable Tie Anchor Mnt, .7"x.5", .18" Hole Dia, .25" Max Tie Width, PA66MP+, Blue, 100/pkg

Article Number 151-00950

Type MCKR6G5

Color Blue (BU)

Quantity Per bag

Product Description Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.

Short Description Metal Cnt Cable Tie Anchor Mnt, .7"x.5", .18" Hole Dia, .25" Max Tie Width, PA66MP+, Blue, 100/pkg

Global Part Name MCKR6G5-PA66MP+-BU

Length L (Imperial)	0.70
Length L (Metric)	17.8
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.46
Width W (Metric)	11.8
Cable Ties	MCT18 - MCT50
Height H (Imperial)	0.35
Height H (Metric)	8.8
Cable Tie Width Max (Imperial)	0.25
Cable Tie Width Max (Metric)	6.4
Mounting Hole Diameter D (Imperial)	0.18
Mounting Hole Diameter D (Metric)	4.5 mm
Mounting Hole Diameter D Min (Imperial)	0.18
Mounting Hole Diameter D Max (Imperial)	0.18
Mounting Hole Diameter D Max (Metric)	4.5

Material	Polyamide 6.6, with metal particles (PA66MP+)
Material Shortcut	PA66MP+
Halogen Free	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00950](#)