

Specification Sheet

Part Number: 151-00982



Integrated design allows for easy insertion by hand.

1–3mm panel thickness range allows for multiple applications.

Double-compression design can accommodate up to 2 wires or cables of varying sizes.

Presents a high extraction force for withstanding extreme conditions.

Heavy Duty Metal Edge Clip, 1–3mm Panel Thickness, 5–7.6mm Cable Range, SS304, 100/bag

Article Number 151-00982

Type MSC2

Color Metal (ML)

Quantity Per bag

Product Description HellermannTyton's Heavy Duty Metal Edge Clip provides an excellent alternative to managing up to 2 wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Heavy Duty Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. This Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

Short Description Heavy Duty Metal Edge Clip, 1–3mm Panel Thickness, 5–7.6mm Cable Range, SS304, 100/bag

Global Part Name MSC2-SS304-ML

Length L (Imperial) 0.95

Length L (Metric) 24.1

Width W (Imperial) 0.50

Width W (Metric) 13.0

Bundle Diameter Min (Imperial) 0.20

Bundle Diameter Min (Metric) 5.0

Bundle Diameter Max (Imperial) 0.30

Bundle Diameter Max (Metric) 7.6

Panel Thickness Min (Imperial) 0.04

Panel Thickness Max (Imperial) 0.12

Panel Thickness Min (Metric) 1.0

Panel Thickness Max (Metric) 3.0

Material Stainless Steel (SS304)

Material Shortcut	SS304
Flammability	Non-burning
Halogen Free	No
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	7326908695

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00982](#)