

## Specification Sheet

Part Number: 151-01113



Head design contains clamping rails to provide full circumferential compression around bundles.

Bent tail allows for quick insertion into head.

Connector Clip, 1.4" Long, PA66HIRHS, Black, 5000/box

**Article Number** 151-01113

**Type** EC46

**Color** Black (BK)

**Quantity Per** carton

**Product Description** Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

**Short Description** Connector Clip, 1.4" Long, PA66HIRHS, Black, 5000/box

<b>Global Part Name</b>	EC46-PA66HIRHSUV-BK
<b>Length L (Imperial)</b>	1.4
<b>Length L (Metric)</b>	35.5
<b>Variant</b>	1.0 - 3.0 mm Edge
<b>Width W (Imperial)</b>	0.44
<b>Width W (Metric)</b>	11.18
<b>Height H (Imperial)</b>	0.56
<b>Height H (Metric)</b>	14.15
<b>Panel Thickness Min (Imperial)</b>	0.04
<b>Panel Thickness Max (Imperial)</b>	0.12
<b>Panel Thickness Min (Metric)</b>	1.0
<b>Panel Thickness Max (Metric)</b>	3.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV

<b>Flammability</b>	UL 94 HB
<b>Operating Temperature</b>	-40°F to +230°F (-40°C to +110°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	5000
<b>Package Quantity (Metric)</b>	5000
<b>Customs Number</b>	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01113](#)