

Specification Sheet

Part Number: 151-01295

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications. Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.



HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.

Connector Clip, 2.0–17.0mm Hole Dia., PA66HIRHSUV, Black, 4000/carton

Article Number 151-01295

Type CC17

Color Black (BK)

Quantity Per carton

Product Description Connector Clips are designed with various fixing point designs, to accommodate the many connectors out in the market. This specific connector clip is designed for a commonly used automotive connector. The width and the height of the fixation point creates minimal rattle when secured. The innovative design of the fir tree creates an interface with four different size holes that are common in the automotive industry. The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.

Short Description	Connector Clip, 2.0–17.0mm Hole Dia., PA66HIRHSUV, Black, 4000/carton
Global Part Name	CC17-PA66HIRHSUV-BK
Length L (Imperial)	1.18
Length L (Metric)	29.9
Fixation Method	Fir Tree
Variant	12.0 x 17.0 mm
Width W (Imperial)	0.80
Width W (Metric)	20.3
Height H (Imperial)	1.03
Height H (Metric)	26.2
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.35
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	9.0
Mounting Hole Diameter D (Imperial)	0.47 x 0.67

Mounting Hole Diameter D (Metric) 12.0 x 17.0 mm

Mounting Hole Diameter D Min (Imperial) 0.47

Mounting Hole Diameter D Max (Imperial) 0.67

Mounting Hole Diameter D Max (Metric) 17.0

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) No

Package Quantity (Imperial) 4000

Package Quantity (Metric) 4000

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01295](#)