

## Specification Sheet

Part Number: 151-01531



Inserts snap precisely into the body of Ratchet Clamps, making installation easy.

Added level of insulation reduces bundle movement in addition to protecting cables and hoses.

Ratchet P-Clamp Size B Soft Insert, TPE, Black, 100/bg

Article Number	151-01531
Type	RCINSERTB
Color	Black (BK)
Quantity Per	bag
Product Description	Soft Inserts snap into the body of HellermannTyton's Ratchet Clamps. They provide an added level of protection for sensitive bundles, especially in high-vibration applications.
Short Description	Ratchet P-Clamp Size B Soft Insert, TPE, Black, 100/bg
Global Part Name	RCINSERTB-TPE-BK

Fixation Method	Others
Variant	Rubber profile
Bundle Diameter Min (Imperial)	0.34
Bundle Diameter Min (Metric)	8.7
Bundle Diameter Max (Imperial)	0.61
Bundle Diameter Max (Metric)	15.5
Material	Thermoplastic Elastomer (TPE)
Material Shortcut	TPE
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Plenum Rating	AH-2
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes

UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01531](#)