

## Specification Sheet

Part Number: 151-01699



Integrated design allows for easy insertion by hand.

1.5–2.0 mm panel thickness range allows for multiple applications.

Double-compression design that accommodates various sizes of wire and cable.

Presents a high extraction force for withstanding extreme conditions.

Low Profile Metal Edge Clip, 1.5 - 2.0mm Panel Thickness, 4.1 - 7mm Cable Range, SS304, 100/bg

Article Number 151-01699

Type MSC2LP

Color Metal (ML)

Quantity Per bag

**Product Description**  
Designed for more confined areas, HellermannTyton's Low Profile Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Metal Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. The Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

**Short Description**  
Low Profile Metal Edge Clip, 1.5 - 2.0mm Panel Thickness, 4.1 - 7mm Cable Range, SS304, 100/bg

Global Part Name MSC2LP-SS304-ML

Length L (Imperial) 0.67

Length L (Metric) 17.0

Width W (Imperial) 0.375

Width W (Metric) 9.50

Bundle Diameter Min (Imperial) 0.161

Bundle Diameter Min (Metric) 4.1

Bundle Diameter Max (Imperial) 0.276

Bundle Diameter Max (Metric) 7.0

Depth D (Imperial) 0.649

Depth D (Metric) 16.48

Panel Thickness Min (Imperial) 0.06

Panel Thickness Max (Imperial) 0.078

Panel Thickness Min (Metric) 1.5

Panel Thickness Max (Metric) 2.0

Material	Stainless Steel (SS304)
Material Shortcut	SS304
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	7326908695

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01699](#)