

Specification Sheet

Part Number: 151-02061



Angled channel allows specific guidance around corners or obstructions.
U-Shape channel provides three sides of protection for wire or bundle.

High-quality polypropylene material with high heat resistance.

Protects against abrasion and other environmental factors.

Mini Channel, 60mm Long, 90 degree 22.5mm radius angle, PPT20, Black, 1000/ctn

Article Number 151-02061

Type 90RADMINICHNL

Color Black (BK)

Quantity Per carton

Product Description The mini-channel family allows a cost effective routing solution that provides protection and configurable routing. Pieces are modular and interchangeable, providing high levels of customization. Mini channels replace engineered channels that are costly to design and develop.

Short Description Mini Channel, 60mm Long, 90 degree 22.5mm radius angle, PPT20, Black, 1000/ctn

Global Part Name 90RADMINICHNL-PPTD20-BK

Length L (Imperial) 2.34

Length L (Metric) 59.5

Width W (Metric) 59.5

Height H (Metric) 1.75

Mounting Hole Diameter D (Imperial) 0.246 - 0.265

Mounting Hole Diameter D (Metric) 6.25 - 6.75 mm

Mounting Hole Diameter D Max (Metric) 6.75

Material Polypropylene 20% Talkum (PPTD20)

Material Shortcut PPTD20

Operating Temperature -40°F to +149°F (-40°C to +65°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02061](#)