

Specification Sheet


Part Number: 151-02949

Easy to install, remove and reposition with just a quarter-turn – no tools necessary.

Multi-directional cable tie slot allows for routing a bundle parallel to or perpendicular to the frame.

Low profile is ideal for cramped spaces.

Designed to fit an 80/20 profile with a T-slot of 8 mm (0.32") and external dimensions of 40 mm (1.5").



Aluminum Frame Mount for 40mm or 1.5" Frame, 4.0 - 4.8mm Panel Thickness, PA66MP+, Blue, 100/bag

Article Number	151-02949
Type	MCAFLM40-1
Color	Blue (BU)
Quantity Per	bag

Product Description Aluminum frame mounts can be used with 20, 30 or 40 mm square frames from the major aluminum frame manufacturers. As there is no need to screw them in place, these mounts offer maximum ease of use and fast installation. The mounts contain metal particles for detection in processing plants where the potential for contamination is undesirable.

Short Description	Aluminum Frame Mount for 40mm or 1.5" Frame, 4.0 - 4.8mm Panel Thickness, PA66MP+, Blue, 100/bag
Global Part Name	MCAFLM40-1-PA66MP+-BU
Length L (Imperial)	1.10
Length L (Metric)	28.0
Width W (Imperial)	0.83
Width W (Metric)	21
Cable Ties	T18 - T50
Height H (Imperial)	0.80
Height H (Metric)	20.2
Cable Tie Width Max (Imperial)	0.49
Cable Tie Width Max (Metric)	12.5
Panel Thickness Min (Imperial)	0.16
Panel Thickness Max (Imperial)	0.19
Panel Thickness Min (Metric)	4.0
Panel Thickness Max (Metric)	4.8

Material	Polyamide 6.6, with metal particles (PA66MP+)
Material Shortcut	PA66MP+
Flammability	UL 94 HB
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02949](#)