

Specification Sheet

Part Number: 151-03645

No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse, 360-degree rotation and reposition capabilities allow for a flexible mounting solution.

Easily remove without leaving residue behind.



Magnetic Clip, Large, 1", Neodymium Magnet/POM/ST, 15lb Pull Force, White, 10/bag

Article Number	151-03645
----------------	-----------

Type	MAGC15L
------	---------

Color	White (WH)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Magnetic clips are designed to route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle by pushing it into the clip and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The clips are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.
---------------------	--

Short Description	Magnetic Clip, Large, 1", Neodymium Magnet/POM/ST, 15lb Pull Force, White, 10/bag
Global Part Name	MAGC15L-NDFEB35/POM/ST-WH
Length L (Imperial)	1.24
Length L (Metric)	31.5
Fixation Method	Magnet
Height H (Imperial)	1.24
Height H (Metric)	31.5
Depth D (Imperial)	0.23
Depth D (Metric)	5.7
Diameter D (Imperial)	0.91
Diameter D (Metric)	23.2
Material	Steel (ST) Neodymium alloy 35M (NDFEB35) Polyacetal (POM)
Material Shortcut	POM NDFEB35 ST
Halogen Free	Yes

UV Resistant (Yes/No)	No
Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	8505110070

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-03645](#)