

Specification Sheet

Part Number: 151-03906



Bolt down one-piece design to bundle and secure two high voltage cables with convoluted tubing.

Compression limiter for high-torque bolted applications.

Integrated M6 Stud Mount acts as third hand for retention while attaching.

Releasable latch for serviceability.

HV Dual Clamp with 120 degree M6 stud mount, 0.94" Bundle Dia, PA66HIRHSUV, Black, 200/ctn

Article Number	151-03906
----------------	-----------

Type	DHVC24M6A
------	-----------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	These high voltage clamps replace expensive four-piece solutions (consisting of a metal bracket, EPDM isolator, tie and stud retainer) with a one-piece locking clamp. The hinged design snaps together to keep bundles separated and secures to any surface with a 6 mm stud or bolt. The wide strap option offers the possibility of a third routing.
---------------------	---

Short Description	HV Dual Clamp with 120 degree M6 stud mount, 0.94" Bundle Dia, PA66HIRHSUV, Black, 200/ctn
-------------------	--

Global Part Name	DHVC24M6A-PA66HIRHSUV-BK
------------------	--------------------------

Length L (Imperial)	4.04
---------------------	------

Length L (Metric)	102.5
-------------------	-------

Fixation Method	Stud Mount
-----------------	------------

Width W (Imperial)	1.20
--------------------	------

Width W (Metric)	30.5
------------------	------

Bundle Diameter Max (Imperial)	0.94
--------------------------------	------

Bundle Diameter Max (Metric)	24.0
------------------------------	------

Bundle Diameter 1st Loop Max (Imperial)	0.94
---	------

Bundle Diameter 1st Loop Max (Metric)	24.0
---------------------------------------	------

Bundle Diameter 2nd Loop Max (Imperial)	0.94
---	------

Bundle Diameter 2nd Loop Max (Metric)	24.0
---------------------------------------	------

Height H (Imperial)	1.26
---------------------	------

Height H (Metric)	32.0
-------------------	------

Mounting Hole Diameter D (Imperial)	0.24
-------------------------------------	------

Mounting Hole Diameter D (Metric)	M6
-----------------------------------	----

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-03906](#)