

## Specification Sheet

Part Number: 151-03975



One-piece ratchet closure design allows for easy installation during pre- or final assembly.

Fine-pitch ratchet increments enable precise sizing around multiple bundle diameters, reducing part inventory versus one-size clamps.

Easy-release feature allows for quick adjustments and maintenance without removal.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.

Mini Ratchet P-Clamp, 0.15 - 0.31" Bundle Dia., 6.5mm Hole Dia., PA66HIRHSUV, Black, 100/bg

Article Number 151-03975

Type 4-8RC6.5PH

Color Black (BK)

Quantity Per bag

**Product Description**

The Mini Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The clamp size and design make it an ideal P-clamp replacement for securing sensor wires, brake lines or other wires. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This release feature allows the clamp to be reused without removing or replacing any bolts or screws.

Short Description	Mini Ratchet P-Clamp, 0.15 - 0.31" Bundle Dia., 6.5mm Hole Dia., PA66HIRHSUV, Black, 100/bg
Global Part Name	4-8RC6.5PH-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	223
Length L (Imperial)	2.66
Length L (Metric)	67.7
Fixation Method	Screw Mounting
Variant	Short
Width W (Imperial)	0.69
Width W (Metric)	17.5
Bundle Diameter Min (Imperial)	0.15
Bundle Diameter Min (Metric)	3.81
Bundle Diameter Max (Imperial)	0.31
Bundle Diameter Max (Metric)	7.874
Mounting Hole Diameter D (Imperial)	0.25
Mounting Hole Diameter D (Metric)	6.5 mm

Mounting Hole Centers (Imperial)	0.98
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar,

electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-03975](#)