

Specification Sheet

Part Number: 156-01346



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.

1-Pc Cable Ties with Pipe Clip, 31-39 mm, PA66HS/PA66HIRHS, Black, 250/pkg

Article Number	156-01346
Type	T50SMVCOC31-39
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	1-Pc Cable Ties with Pipe Clip, 31-39 mm, PA66HS/PA66HIRHS, Black, 250/pkg

Global Part Name T50SMVCOC31-39-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 222

Length L (Imperial) 8.3

Length L (Metric) 210.0

Fixation Method Omega Clips

Identification Plate Position none

Width W (Imperial) 0.19

Width W (Metric) 4.7

Bundle Diameter Min (Imperial) 0.08

Bundle Diameter Min (Metric) 2.0

Bundle Diameter Max (Imperial) 2.0

Bundle Diameter Max (Metric) 50.0

Thickness T (Metric) 1.35

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01346](#)