

## Specification Sheet

Part Number: 156-01789



Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

Cable tie accommodates wide range of secondary bundle sizes.

MOC Clip, 14 mm Transverse, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

**Article Number**

156-01789

**Type**

T50SMVCMOC14M180

**Color**

Black (BK)

**Quantity Per**

carton

**Product Description**

The MOC 180 to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The clip's orientation allows the second routing to be assembled in the direction of the first routing. The swivel coupler allows the two routings to rotate independently of each other.

**Short Description**

MOC Clip, 14 mm Transverse, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

**Global Part Name** T50SMVCMOC14M180-PA66HIRHSUV-BK

**Minimum Tensile Strength (Imperial)** 50.0

**Minimum Tensile Strength (Metric)** 225

**Length L (Imperial)** 0.82

**Length L (Metric)** 20.9

**Fixation Method** Omega Clips

**Identification Plate Position** none

**Bundle Diameter Min (Imperial)** 0.51

**Bundle Diameter Min (Metric)** 13.0

**Bundle Diameter Max (Imperial)** 0.62

**Bundle Diameter Max (Metric)** 15.8

**Height H (Imperial)** 1.50

**Height H (Metric)** 38.2

**Depth D (Imperial)** 0.39

**Depth D (Metric)** 10.0

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +230°F (-40°C to +110°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01789](#)