

Specification Sheet

Part Number: 156-01797

Low-profile clip attaches easily to plastic and metal edges as thin as 0.5 mm and up to 2.5 mm without the need for a mounting hole.

Two designs allow bundles to be secured parallel or vertical to surface edges.

Provides low insertion force and high extraction force – ideal for assembly environments.

Two-piece assembly allows the mount to slide along the strap, ensuring proper orientation.

Cable tie is outside serrated to reduce bundle chafing.



Article Number	156-01797
----------------	-----------

Type	T30ROSEC0.5-2.5SP-SVA
------	-----------------------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
---------------------	--

Short Description	Cable Tie/Edge Clip, 5.7"L, 0.5–2.5 mm Panel, Parallel, 30lb, PA66HS/PA66HIRHS, BK, 500/pkg
Global Part Name	T30ROSEC0.5-2.5SP-SVA-PA66HS/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	30.0
Minimum Tensile Strength (Metric)	133
Length L (Imperial)	5.7
Length L (Metric)	145.0
Fixation Method	EdgeClip, sideways, assembled, 2 piece
Identification Plate Position	none
Variant	Outside Serrated
Width W (Imperial)	0.13
Width W (Metric)	3.4
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	30.0

Height H (Imperial)	0.05
Height H (Metric)	1.2
Panel Thickness Min (Imperial)	0.01
Panel Thickness Max (Imperial)	0.1
Panel Thickness Min (Metric)	0.5
Panel Thickness Max (Metric)	2.5
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500

Package Quantity (Metric)	500
----------------------------------	-----

Customs Number	3926909988
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01797](#)