

## Specification Sheet

Part Number: 156-01813

Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Fixed connector controls routing orientation.

Cable tie accommodates wide range of secondary bundle sizes.



MOC Clip, 7 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 2500/ctn

**Article Number**

156-01813

**Type**

T50RMOC7SAD-SET

**Color**

Black (BK)

**Quantity Per**

carton

**Product Description**

The MOC with Saddle to T50R Tie has a two-piece design that keeps two routings secured together while providing a fixed orientation for each bundle. The bi-directional saddle design allows the bundles to be coupled parallel or perpendicular to one another. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness.

**Short Description**

MOC Clip, 7 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 2500/ctn

**Global Part Name** T50RMOC7SAD-SET-PA66HIRHSUV-BK

**Minimum Tensile Strength (Imperial)** 50.0

**Minimum Tensile Strength (Metric)** 225

**Length L (Imperial)** 0.46

**Length L (Metric)** 11.6

**Fixation Method** Omega Clips

**Identification Plate Position** none

**Releasable Closure** No

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Bundle Diameter Min (Imperial)** 0.24

**Bundle Diameter Min (Metric)** 6.0

**Bundle Diameter Max (Imperial)** 0.31

**Bundle Diameter Max (Metric)** 8.0

**Height H (Imperial)** 0.76

**Height H (Metric)** 19.4

<b>Depth D (Imperial)</b>	0.39
<b>Depth D (Metric)</b>	10.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	2500
<b>Package Quantity (Metric)</b>	2500
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01813](#)