

## Specification Sheet

Part Number: 156-01855



Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Clip and clamp both offer easy bundle installation.

Independent rotation allows for adjustable routing orientation.

Locking clamp dynamically fits a range of bundle sizes.

LOC Locking Clamp, 10-14 mm, to MOC Clip, 7 mm, PA66HIRHSUV, Black, 2500/ctn

**Article Number** 156-01855

**Type** MOC7FLOC10-14

**Color** Black (BK)

**Quantity Per** carton

**Product Description** The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description** LOC Locking Clamp, 10-14 mm, to MOC Clip, 7 mm, PA66HIRHSUV, Black, 2500/ctn

**Global Part Name** MOC7FLOC10-14-PA66HIRHSUV-BK

<b>Length L (Imperial)</b>	1.63
<b>Length L (Metric)</b>	41.30
<b>Variant</b>	Clip to Clamp
<b>Bundle Diameter Min (Imperial)</b>	0.24
<b>Bundle Diameter Min (Metric)</b>	6.0
<b>Bundle Diameter Max (Imperial)</b>	0.31
<b>Bundle Diameter Max (Metric)</b>	8.0
<b>Height H (Imperial)</b>	1.08
<b>Height H (Metric)</b>	27.4
<b>Depth D (Imperial)</b>	0.47
<b>Depth D (Metric)</b>	12.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB

<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	2500
<b>Package Quantity (Metric)</b>	2500
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01855](#)