

## Specification Sheet

Part Number: 156-02201



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip Perpendicular, 26 mm, 7 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

**Article Number** 156-02201

**Type** MOC26FMOC7M180

**Color** Black (BK)

**Quantity Per** carton

**Product Description** The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

**Short Description** MOC Clip to MOC Clip Perpendicular, 26 mm, 7 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

**Global Part Name** MOC26FMOC7M180-PA66HIRHSUV-BK

|                                       |                                                                          |
|---------------------------------------|--------------------------------------------------------------------------|
| <b>Length L (Imperial)</b>            | 2.05                                                                     |
| <b>Length L (Metric)</b>              | 51.99                                                                    |
| <b>Variant</b>                        | Clip to Clip Transverse                                                  |
| <b>Bundle Diameter Min (Imperial)</b> | 0.91                                                                     |
| <b>Bundle Diameter Min (Metric)</b>   | 23.0                                                                     |
| <b>Bundle Diameter Max (Imperial)</b> | 1.14                                                                     |
| <b>Bundle Diameter Max (Metric)</b>   | 29.0                                                                     |
| <b>Height H (Imperial)</b>            | 1.61                                                                     |
| <b>Height H (Metric)</b>              | 41.0                                                                     |
| <b>Depth D (Imperial)</b>             | 0.47                                                                     |
| <b>Depth D (Metric)</b>               | 12.0                                                                     |
| <b>Material</b>                       | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| <b>Material Shortcut</b>              | PA66HIRHSUV                                                              |
| <b>Flammability</b>                   | UL 94 HB                                                                 |

|                                    |                                   |
|------------------------------------|-----------------------------------|
| <b>Halogen Free</b>                | Yes                               |
| <b>Operating Temperature</b>       | -40°F to +230°F (-40°C to +110°C) |
| <b>ROHS Compliant</b>              | Yes                               |
| <b>Package Quantity (Imperial)</b> | 2000                              |
| <b>Package Quantity (Metric)</b>   | 2000                              |
| <b>Customs Number</b>              | 3926909988                        |

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02201](#)