


## Specification Sheet

Part Number: 156-02307



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip, 7 mm, 9 mm, PA66HIRHSUV, Black, 2000/ctn

**Article Number** 156-02307

**Type** MOC7FMOC9M

**Color** Black (BK)

**Quantity Per** carton

**Product Description** The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

**Short Description** MOC Clip to MOC Clip, 7 mm, 9 mm, PA66HIRHSUV, Black, 2000/ctn

**Global Part Name** MOC7FMOC9M-PA66HIRHSUV-BK

<b>Length L (Imperial)</b>	1.25
<b>Length L (Metric)</b>	31.7
<b>Variant</b>	Clip to Clip
<b>Bundle Diameter Min (Imperial)</b>	0.24
<b>Bundle Diameter Min (Metric)</b>	6.0
<b>Bundle Diameter Max (Imperial)</b>	0.31
<b>Bundle Diameter Max (Metric)</b>	8.0
<b>Height H (Imperial)</b>	0.68
<b>Height H (Metric)</b>	17.2
<b>Depth D (Imperial)</b>	0.39
<b>Depth D (Metric)</b>	10.0
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB

<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	2000
<b>Package Quantity (Metric)</b>	2000
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02307](#)