

Specification Sheet

Part Number: 156-02354



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip, 14 mm, 26 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number 156-02354

Type MOC14FMOC26M

Color Black (BK)

Quantity Per carton

Product Description The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Short Description MOC Clip to MOC Clip, 14 mm, 26 mm, PA66HIRHSUV, Black, 1000/ctn

Global Part Name MOC14FMOC26M-PA66HIRHSUV-BK

Length L (Imperial)	2.35
Length L (Metric)	59.7
Variant	Clip to Clip
Bundle Diameter Min (Imperial)	0.51
Bundle Diameter Min (Metric)	13.0
Bundle Diameter Max (Imperial)	0.62
Bundle Diameter Max (Metric)	15.8
Height H (Imperial)	1.61
Height H (Metric)	41.0
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02354](#)